



TELEX

Radio Dispatch

Radio Dispatch Engineering Group

C-Soft Version 5.100 Engineering Release Notes

Notice:

The content in this document represents the current view of Bosch Security Systems as of the date of publication. Because Bosch Security Systems responds continually to changing market conditions, this document should not be interpreted as a commitment on the part of Bosch Security Systems. Bosch Security Systems cannot guarantee the accuracy of any information presented after the date of publication.

Bosch Security Systems, Inc. All rights reserved

SFT000061000 – Rev D

June 24, 2010

Table of Contents

1. Revision History	1
2. Overview.....	1
3. New Features	1
4. Improved Features and Fixed Issues	1
Version 5.100	1
5. Compatibility.....	1
Version 5.100	1
6. Installation and Upgrade.....	2
Version 5.100	2

1. Revision History

Revision	Date	Author	Description
A	08/07/2009	Radio Dispatch Engineering Group	Initial draft C-Soft Version 4.200
B	09/11/2009	Radio Dispatch Engineering Group	Updated to C-Soft Version 4.300
C	03/31/2010	Radio Dispatch Engineering Group	Updated to C-Soft Version 5.000
D	06/24/2010	Radio Dispatch Engineering Group	Updated to C-Soft Version 5.100

2. Overview

This is the release notes for C-Soft Version 5.100 firmware/software. This release contains new features, improved features, and fixed issues. The release notes include all of the changes and fixes since official release Version 5.000.

3. New Features

Version 5.100

- Runtime
 - o Added Keep Alive feature for the ADHB-4 to use in case of a USB failure.
 - o Added version information exchange between ADHB-4 and C-Soft.
 - o Added in ability for ADHB-4 to popup a message box on C-Soft with information if it needs to give the user important information.
 - o Added new Dongle Driver code to work with Windows 7.

4. Improved Features and Fixed Issues

Version 5.100

- Designer
 - o Relay Button Time entry fixed.
- Runtime
 - o Timed Relay will now turn off when very short time durations are entered.
 - o Phones can no longer go on hold when not off hook.
 - o NENA hold state is now held when USB is unplugged.
 - o Issue with using SIP, Phone and NENA in a certain pattern no longer goes to incorrect speaker.

5. Compatibility

Version 5.100

- Compatible with IP-223 Version 4.300
- Compatible with ADHB-4 Version 1.000 and 1.100

6. Installation and Upgrade

Version 5.100

- To Install C-Soft double click on the Setup executable.
 - o Follow the steps in the installation instructions.
 - o At the end of C-Soft installation the Dongle Key Driver will be asked to install.
 - o If installing on Windows 7 there will be an extra step for installing the drivers, this step does not occur in Windows XP.
 - o When connecting an ADHB-4 to a Windows XP computer the user must select the location of the drivers to install. These will be located at "C:\Program Files\Telex Communications\C-Soft\usb_drivers".
 - o When connecting an ADHB-4 to a Windows 7 computer the drivers will automatically install, and the user will not need to do anything for that.
- To Upgrade C-Soft a new installation program can be run, or if the install package has already been done once the new Runtime and Designer executables can be copied over the old ones in the program folder where they are located.